



# Pas Reform Manual candling table

For identifying clear or infertile eggs in a  
full setter tray



Pas Reform  
Hatchery Technologies



# Manual candling table

Visual inspection quickly identifies clear or infertile eggs

## Benefits

Large capacity candling table illuminates a full setter tray of eggs, with a halogen light assembly underneath to visually identify clear or infertile eggs. Ideal for candling smaller batches of eggs or for analyzing sample trays from larger batches. Easy to clean stainless steel construction, mounted on swivel castor wheels for easy manoeuvrability. When equipped with a (roller) conveyor, trays can be automatically transported for optimal working conditions.

## How it works

- In the cover of the candling table, 126, 150 or 162 holes (depending on tray type) correspond to the centre of the eggs on the setter tray
- After positioning the setter tray, the cover is lifted by a handle which positions the eggs over the holes in the table
- Eggs without embryonic development allow more light to pass through and are therefore easily identified for manual removal
- The setter tray without infertile eggs can then continue either via a transfer system to hatcher baskets, or be returned to the setter when candling is carried out prior to day 18

## Related products

- ▶ SmartTray™ 126
- ▶ SmartTray™ 150
- ▶ SmartTray™ 162
- ▶ Egg transfer system
- ▶ Container

## Technical Specifications

Capacity	> 20,000 hatching eggs/hour (depending on fertility level)
Installed power	> 1.0 kW
Material	> Stainless steel AISI304 (where applicable)
Dimensions (LxWxH)	> 650 x 850 x 950 mm
Weight	> 56 kg



**Pas Reform**  
**Hatchery Technologies**

P.O. Box 2  
7038 ZG Zeddam  
The Netherlands

Phone +31 314 659 111  
Fax +31 314 652 575  
info@pasreform.com  
www.pasreform.com